

OPTION LED-LAMP

1. SPECIFICATIONS

Model	RMT-L1300A	RMT-L1600A	RMT-L2000A
Packaging Dimensions (LxD)	5.9 x 0.27ft (180 x Ø8.2cm)	7.6 x 0.27ft (230 x Ø8.2cm)	9.2 x 0.27ft (280 x Ø8.2cm)
Packaging Weight	4.41lbs (2.0kg)	6.61lbs (3.0kg)	8.82lb (4.0kg)
Applicable Trimmer	RMT-1300	RMT-1600	RMT-2000

2. INSTALL

Assemble Option Lamp

Follow these steps to assemble optional LED-LAMP.

1. Remove the support with a screwdriver (fig.1).
2. Install the lamp bracket and the support onto the frame(support is in the middle of the frame) with supplied screws (3pieces) (fig.2).
3. Adjust the angle of the support to be vertical, and then screw down the bolt 1. Adjust the height of the bolt 2 just to touch the workbench (fig.3).
4. Fix the redundant power lines tightly with supplied screws and binding wires (fig.4).
5. Connect the LED lamp with the power cord connector (fig.5).

SPECIAL ATTENTION: Be sure to cut off the electricity supply during the installation process.



Fig.1



Fig.2



Fig.3



Fig.4



Fig.5

